Ground-based, Scanning Water Vapor DIAL Reference Systems

Volker Wulfmeyer, Gerd Wagner, Max Shiler, Anna Petrova, Andreas Behrendt, Thorsten Schaberl, IPM Ulla Wandinger, Dietrich Althausen, Andrea Riede, IfT Martin Ostermeyer, Alexander Strässer, Ralf Menzel, University of Potsdam Martin Wirth, Andreas Fix, Gerhard Ehret, DLR Oberpfaffenhofen Shane Mayor, Scott Spuler, Tammy Weckwerth, NCAR ATD






1. Motivation

- Large gaps in our knowledge of the global water vapor distribution is a major hindrance for progress in atmospheric sciences
- Water vapor DIAL is a key technology which has the potential to revolutionize our knowledge of atmospheric processes
- Simultaneously significant advances in weather and climate research can be expected



Expected performance of scanning water vapor DIAL






2. DFG Project goal and design

- Development of a water vapor lidar reference system based on a high-power laser transmitter using the DIAL technique
 - P1: High-power pump laser, 400 W (UP)
 - P2: Ti:Sapphire frequency converter, 20 W (UHOH, DLR)
 - P3: Mobile platform with scanner (IfT)
- Key features:
 - mobile
 - operational
 - 3-d scanning
 - simultaneously high resolution, accuracy and range
 - demonstrator for airborne and space borne systems



Relation between the projects



Boundary conditions considered for space borne DIAL: - 1% overall eff. - 10% pump laser eff. - 50% doubler - 20% frequ. conv.

Currently no demonstrator



Universitä
· • 10 👘
orsdam.

P1: High-power pump laser

a dam	Diode laser pumped → 400 W average pow → 10-100 ns pulse du → Rep. rate 100-1000 → M ² < 1.5 → Single-frequency o → High wall-plug effic	ver, scalable tration Hz operation by injection seeding	
Frequency quadrupling 266 nm: - Ozone DIAL - Aerosol lidar	Frequency tripling 355 nm: - Ozone DIAL - Aerosol lidar - Temperature Raman lidar - Water vapor Raman lidar - HSRL (EARTHCARE reference system) - Incoherent Doppler lidar (ADM Reference system)	Frequency doubling 532 nm: - Aerosol lidar - Water vapor DIAL by means of frequency conversion to 800-950 nm (WALES reference system)	Fundamental 1064 nm: - Aerosol lidar Using frequency conversion with OPO or Cr ⁴⁺ :YAG to > 1400 nm: - Eye-safe aerosol lidar - Coherent Doppler lidar - DIAL

September 15/16, 2004 3rd Workshop "Lidar Research Water Vapor and Wind", UHOH

1818


Goals of P1:

Development of a pump laser with the following specs:

- 1. Full diode laser pumped
- 2. Efficiency: > 10 % overall wall-plug (incl. cooling, etc.)
- 3. Average power: > 400 W
- 4. Repetition rate: 100-1000 Hz (lower rep. rates preferred)
- 5. Pulse duration: 10-100 ns
- 6. Beam quality: $M^2 < 1.5$
- 7. Frequency stability: optionally injection seeding
- 8. Potential of scalability
- 9. Operational
- 10. Frequency doubling with > 50 % efficiency








Envisioned set up: Single dynamically stable, unidirectional ring resonator







P2: UHOH pump laser





IB-Laser High-power Pump Laser System: 67 W @ 1064 nm (250 Hz), M² = 1.5, final goal: 100 W 25 W @ 532 nm (250 Hz), M² = 2, final goal: 50 W













Frame 18



 $M_{X}^{2} = 2,20$ $M_{y}^{2} = 2,33$ Astigm.= 0,33 Asymm.=1,04







Frame 13





Goals of P2:

Development of a Ti:Sapphire laser with the following specs:

- 1. Pumped by laser developed in task 1
- 2. Wavelength: 810-820 nm
- 3. Conversion efficiency > 20 % (laser pump wavelength)
- 4. Pulse duration: 10-100 ns
- 5. Beam quality: $M^2 < 2$
- 6. Frequency stability: 60 MHz
- 7. Spectral Bandwidth: 120 MHz
- 8. Spectral purity: > 99.95 %
- 9. Alternating dual frequency operation for DIAL measurements (frequency separation 10 < 100 GHz)
- 10. Operational

11. Compact design for application on mobile platform

Two DIAL transmitter are under development, one system will be incorporated in DFG system, the other one will be delivered to NCAR/ATD.

Simultaneously, an eye-safe DIAL transmitter development is ongoing based on Cr⁴⁺:YAG. Performance simulations are promising.





P3: Mobile, scanning platform

Goals of P3:

Development of a water vapor DIAL system:

- 1. Operational (automatized)
- 2. Mobile
- 3. Scanning
- 4. Coated for 800-1600 nm
- 5. Telescope diameter: 1 m
- 6. State-of-the-art daylight background suppression
- 7. Low noise receiver for near-infrared region
- 8. Design optimized for eye-safe operation
- 9. Software for data analysis including error analysis



Strong collaboration with NCAR/ATD



Status and goals

- Two DIAL system developments going on in Germany and US
- DFG funding: €2M
- UHOH/NCAR system funding: internal, 1.2M€
- Strong collaboration and coordination
- First test measurements planned in Spring 2005 at UHOH:
 - transmitter from UHOH
 - large receiver from NCAR/ATD
 - validation using NCAR reference radiosondes
- First field operation:

DFG Research Project QPF, Summer 2007, with two systems

